


X axis | P12.X100S/K

Aperture Ø25mm | Piezo Nanopositioning Stages



Introduction

P12.X100 is X axis motion piezo scanning stage. The piezo scanner could realize displacement of 100µm. The aperture diameter as 25mm, which is suitable for lighttransmitted applications such as microscopy.

Characteristics >>

- X motion
- Travel to 100µm
- Load capacity to 0.8kg
- Optional UHV compatible version
- Closed-loop version for high repeatability

Applications >>

- Scanning interference
- Surface measurement
- Optical capture
- Confocal microscopy
- Wafer positioning
- Image processing and stabilization



Harbin Core Tomorrow Science & Technology Co., Ltd.

Tel: +86-451-86268790 Email: info@coremorrow.com
Fax: +86-451-86267847 Web: www.coremorrow.com

Headquarters: Building I2, No.191 Xuefu Road, Nangang District, Harbin
Shanghai Office: Building 2, No.608 Shengxia Road, Pudong District, Shanghai

Technical Data >>

Type	S-Closed loop K-Open loop	P12.X100S	P12.X100K	Units
Active axes		X	X	
Travel range(0~120V)		80	80	$\mu\text{m}\pm 10\%$
Travel range(0~150V)		100	100	$\mu\text{m}\pm 10\%$
Sensor		SGS	-	
Aperture		$\varnothing 25$	$\varnothing 25$	mm
Closed/open loop resolution		3	1	nm
Linearity		0.05	-	%F.S.
Repeatability		0.02	-	%F.S.
Pitch/yaw/roll		<10	<10	μrad
Push/pull force		30/10	30/10	N
Stiffness		0.3	0.3	$\text{N}/\mu\text{m}\pm 20\%$
Unloaded resonant frequency		230	230	$\text{Hz}\pm 20\%$
Closed/open-loop unloaded step time		10	0.8	$\text{ms}\pm 20\%$
Load capacity		0.8	0.8	kg
El. capacitance		1.8	1.8	$\mu\text{F}\pm 20\%$
Operating temperature ^[1]		-20~80	-20~80	$^{\circ}\text{C}$
Material		Steel, Al	Steel, Al	
Size(L×W×H)		60×60×24	60×60×24	mm
Mass		140	140	$\text{g}\pm 5\%$
Cable length ^[2]		1.5	1.5	$\text{m}\pm 10\text{mm}$
Connector ^[2]		-	-	


Note: Max driving voltage could be -20V~150V, 0~120V is recommended for long-term and high-reliable operation. Unless otherwise specified, the above parameters are measured at room temperature about 25°C.

[1] Custom ultralow temperature and ultrahigh vacuum versions are available.




[2] Custom cable length and connector is available.

Note: The parallelism of the moving platform is about 20 μm , and the roughness is about 1.6 to 3.2. Please contact the sales engineer for confirmation before purchase.

Drawing >>



Curves >>



Disclaimer: The data here are typical, only for reference. Some variations will occur for different batch.

Recommended Controllers >>



E01.D1
LCD, membrane button, up to 625mA
RS-232/RS-422/USB interface
Software secondary development



E53
Small size, 60mA
RS-232/RS-422/USB interface
Software secondary development



Harbin Core Tomorrow Science & Technology Co., Ltd.

Tel: +86-451-86268790 Email: info@coremorrow.com
Fax: +86-451-86267847 Web: www.coremorrow.com

Headquarters: Building I2, No.191 Xuefu Road, Nangang District, Harbin
Shanghai Office: Building 2, No.608 Shengxia Road, Pudong District, Shanghai