

# $\theta_x, \theta_y$ axes | P34.T2S/K-B2

## Piezo Tip/Tilt Platform



### Characteristics >>

- $\theta_x, \theta_y$  tilt
- Tilt range to 2.8mrad/axis
- Sub-ms response time
- High closed-loop positioning accuracy
- High temperature stability

### Applications >>

- Laser scanning
- Image processing and stabilization
- Beam deflection
- Interlacing scanning, dithering
- Interference
- Light filter/optical switch
- Laser micromachine
- Active and adaptive optics

## Introduction

P34.T2-B2 piezoelectric deflection platform is designed for lenses large up to 80 mm in diameter. Their differential drive exhibits excellent angular positioning stability over a wide temperature range. P34.T2-B2's structure allows the top platform to perform high dynamic precision deflection motion on two orthogonal axes with common pivot points.



**Harbin Core Tomorrow Science & Technology Co., Ltd.**

Tel: +86-451-86268790 Email: [info@coremorrow.com](mailto:info@coremorrow.com)  
Fax: +86-451-86267847 Web: [www.coremorrow.com](http://www.coremorrow.com)

Headquarters: Building I2, No.191 Xuefu Road, Nangang District, Harbin  
Shanghai Office: Building 2, No.608 Shengxia Road, Pudong District, Shanghai

## Technical Data >>

Type	S - closed loop K - open loop	P34.T2S-B2	P34.T2K-B2	Units
Active axes		$\theta_x, \theta_y$	$\theta_x, \theta_y$	
Driving channels		3	3	
Tilt angle (0~120V)		2.2		mrad $\pm 20\%$
Tilt angle (0~150V)		2.8		mrad $\pm 20\%$
Integrated sensor		SGS	-	
Resolution		0.2	0.1	$\mu$ rad
Closed-loop linearity		0.1	-	%F.S.
Closed-loop repeatability		0.02	-	%F.S.
Unloaded resonant frequency		2.8	2.8	kHz $\pm 20\%$
El. capacitance		7.2/axis	7.2/axis	$\mu$ F $\pm 20\%$
Operating temperature <sup>[1]</sup>		-20~80	-20~80	°C
Material		Aluminum	Aluminum	
Platform Length L		56	56	mm $\pm 0.1$
Mass		500	500	g $\pm 5\%$
Cable length <sup>[2]</sup>		1.5	1.5	m $\pm 10$ mm


Note: Technical data are measured by CoreMorrow E00/E01 series piezo controller. Max driving voltage could be -20V~150V, 0~120V is recommended for long-term and high-reliable operation. Unless otherwise specified, the above parameters are measured at room temperature about 25° C.

[1] Custom ultralow temperature and ultrahigh vacuum versions are available.

[2] Custom cable length and connector is available.

Note: The parallelism of the moving platform is about 20 $\mu$ m, and the roughness is about 1.6 to 3.2. Please contact the sales engineer for confirmation before purchase.

## Drawing >>



## Recommended Controllers >>



### E01.D3

LCD, membrane button, up to 625mA  
 RS-232/RS-422/USB interface  
 Software secondary development



### E70

Small size, ave current 70mA/channel  
 RS-232/RS-422/USB interface  
 Software secondary development



## Harbin Core Tomorrow Science & Technology Co., Ltd.

Tel: +86-451-86268790

Email: [info@coremorrow.com](mailto:info@coremorrow.com)

Headquarters: Building I2, No.191 Xuefu Road, Nangang District, Harbin

Fax: +86-451-86267847

Web: [www.coremorrow.com](http://www.coremorrow.com)

Shanghai Office: Building 2, No.608 Shengxia Road, Pudong District, Shanghai